



Aculon-HB Hydrophilic Use Instructions

Product Description

Aculon HB is a water based specialty coating that supplies Hydrophilic properties.

Substrate:

Use on any glass or metal substrate. This product may be used on plastics, but should be tested to determine its effectiveness.

Mixing & Bath setup:

The product is ready to use as provided. If any bath will be subject to environmental contamination, recirculate the solution through a 0.2 micron polypropylene media filter.

The product should be used at room temperature.

Dip tanks should be made of polypropylene or PTFE polymers.

This product may also be wipe applied.

Application

Typical use:

1. Dip your previously cleaned substrate in the Aculon HB bath for 1 min
2. Remove the substrate
3. Blow dry the substrate with oil free air and buff as needed.
4. Once dry, your substrate will exhibit Hydrophilic properties
5. This material may be reapplied as needed.