

OPTOLINQ TMC-2100



Optically clear epoxy molding compound

- Exceptional moldability with long spiral flow
- Low moisture absorption even at high temperature and high humidity conditions
- Excellent reliability

OPTOLINQ TMC-2100 is an optically clear epoxy molding compound specifically designed for the encapsulation of optoelectronic devices. With its high spiral flow, it ensures precise and intricate molding. **TMC-2100** offers excellent moisture resistance, maintaining performance even in high temperature and humidity conditions. **TMC-2100** stands out with its superior moldability and reliability, ensuring good quality and precision in optoelectronic device molding.

Cured properties¹

Property	Value	Unit
Specific gravity	1.20–1.25	–
Hardness at 25 °C	>80	Shore D
Gel time at 150 °C	35–60	s
Spiral flow at 150 °C	80–180	cm
Mold shrinkage	<1.5	%
Glass transition temperature by TMA	120±10	°C
Coefficient of thermal expansion, α1	60–100	ppm/K
Coefficient of thermal expansion, α2	170–210	ppm/K
Flexural strength	110	MPa
Flexural modulus	2.6–3.4	GPa
Transmittance at 400 nm ²	>85	%

¹ Samples were cured using the following parameters. In mold cure: 4 min at 150 °C, Post-mold cure: 4 h at 150 °C

² Sample thickness is 1 mm.

Recommended mold parameters

Parameter	Value	Unit
Preheat temperature	75–95	°C
Molding temperature	155–165	°C
Molding pressure	3–8	MPa
Transfer time at 165 °C	40–60	s
Cure time at 165 °C	2.5–4	min
Post mold cure time at 165 °C	3–4	h

Europe

Industrieweg 15E,
1566JN Assendelft
The Netherlands
Phone: +31 (20) 893 2224
Email: info@caplinq.com

Canada

80 Sirocco Crescent
Ottawa ON, K2S 2C9
Canada
Phone: +1 (613) 482-2215
Email: info@caplinq.com



North America

36927 Schoolcraft Rd
Livonia, MI 48150
United states
Phone: +1 (313) 558-8243
Email: info@caplinq.com

South East Asia

S-08-07 Persiaran Triangle
B Lepas, Penang 11900
Malaysia
Phone: +60(12)4302223
Email: info@caplinq.com

Processing Instructions

- Before use, allow **TMC-2100** to reach room temperature (20 ± 5 °C, $40\pm 15\%$ RH) for a minimum of 24 hours for larger pellets and 12 hours for smaller ones, ensuring the bag remains unopened to prevent moisture contamination.
- For **TMC-2100** in larger sizes, preheating can be performed using standard RF equipment. Preheating must be done slowly to achieve uniform temperature.
- Apply an outer releasing agent, such as silicones or fluorinated compounds, to the mold surface to facilitate easy release from the mold dies.
- Prior to molding with **TMC-2100** or any new material, the mold should be cleaned thoroughly. To prepare the mold, the initial three shots should be cured for 5–10 minutes. After this initial preparation period, you can reduce the curing time to a level that provides sufficient hot hardness for effective release.

Please note that the provided information is based on available data and typical conditions. For specific applications and detailed test results, refer to the actual test data and conduct appropriate certifications.

Storage and Handling

OPTOLINQ TMC-2100 is available in pressed pellets in a wide range of sizes to meet specific customer needs. To ensure product integrity, keep it away from oxidizing materials. For long-term storage, maintain a cold environment, ideally at -10°C or lower. The shelf life under this condition is 6 months.